



GL4C4C

by Burndy
Catalog ID: GL4C4C

Prop 65 Notice

Mechanical Grounding Connector, 2 Copper Cables to Bar, 8 AWG (Sol.) - 4 AWG (Str.) (Run & Tap), 3/8" Stud

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Physical Attribute - Screw Type	Hexagonal Bolt
Plated	N
Plating Type	Unplated
UPC	781810260005
UPC 12 Digit	7818102600055

Dimensions

Dimension - B Length inch	1.25 in
Dimension - D inch	1.44 in
Dimension - F Width Center to Center inch	0.94 in
Dimension - Height fraction	1-1/2 in
Dimension - Height inch	1.50 in
Dimension - Length Side B inch	1.88 in
Dimension - Pad Width inch	0.75 in
Dimension - Width fraction	1-3/8 in
Dimension - Width inch	1.38 in
Dimension - Width mm	35 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Solid Size Range	8 AWG-4 AWG
Conductor - Copper Str Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG
Conductor - Copper Str Size Range	8 AWG-4 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)