



GP1126

by Burndy
Catalog ID: GP1126

Prop 65 Notice

Cu Alloy Ground Connector, 2 Cables to Rod or Pipe, 1/2" Rod Dia., 1/4" IPS(A), #4 Sol - 2/0 Str AWG Cu Cable(AA), 3/8" Bolt

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	271
UPC	781810260517
UPC 12 Digit	7818102605177

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in
Dimension - Width mm	48 mm

Conductor Related

Conductor - Rod Size	1/2 in
Conductor Size	#4 AWG Sol - 2/0 AWG Str

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)