



GP1526G1

by Burndy
Catalog ID: GP1526G1

Prop 65 Notice

Raised Floor Grounding Clamp, #8 Sol. - 2/0 Str., 1.69 in L, 2.62 in W

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round
Plated	N
Plating Type	Unplated
U Bolt Type	UB244
UPC	781810042823
UPC 12 Digit	7818100428233

Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.75 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	2.62 in
Dimension - Width mm	67 mm

Conductor Related

Conductor Size	#8 Sol AWG - 2/0 Str AWG
Number Of Conductors	1;2

Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)