



## GP64526G1

by Burndy  
Catalog ID: GP64526G1

Prop 65 Notice

Raised Floor Grounding Clamp, #4 Sol. - 2/0 Str., 1.69 in L, 2.38 in.

Features: Accepts 1 Or 2 Ground Conductors, Requires Less Connectors To Install Signal Reference Grid, Made Of Copper Alloy, DURIMUM U-Bolts, Nuts And Lockwashers, Provides A Low Impedance Ground Path For Maximum Performance, Grounds All Pedestals (Round Or Square), Will Handle From 3/4 IN To 1 IN Round Or Square, Ease Of Installation, Serves 3 Needs, 1, Signal Reference Grid, 2, Static Ground, 3, Fault Current Ground, Connectors Solves All Possible Grounding Problems Found In Computer Applications Today, UL467 Listed, Width: 2.38 IN, Length: 1.69 IN, Pedestal Type: 3/4 - 1 IN Round, 3/4 - 7/8 IN Square, Dimension B: 1.5 IN

## Product Details

### General

Application	For Raised Floor Systems
Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy, Cast
Material - Hardware	DURIUM™ Silicon Bronze
Pedestal Type	Round;Square
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GP-G1
U Bolt Type	UB222
UPC	781810828014
UPC 12 Digit	7818108280144

### Dimensions

Bolt Size	3/8 in
Dimension - B Length inch	1.50 in
Dimension - L Length Overall mm	43 mm
Dimension - Length Overall inch	1.69 in
Dimension - Width inch	2.38 in
Dimension - Width mm	60 mm

### Conductor Related

Conductor - Copper Solid Size Range	4 AWG
Conductor - Copper Str Size Range	2/0 AWG
Conductor Size	#4 AWG Sol - 2/0 AWG Str
Conductor Type	CU C Str-Size
Number Of Conductors	1;2

## Certifications and Compliance

Certification - CSA Approved	No
Certification - UL Listed Direct Burial	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)