



GQ2929

by Burndy
Catalog ID: GQ2929

Prop 65 Notice

Cu Ground Connector, 2/0 AWG Str - 250 Kcmil Cu, 6" IPS, Cable to Tube

Product Details

General

Installation Torque Recommended in-lb	480 LBS/in
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	247;291
UPC	781810260616
UPC 12 Digit	7818102606166

Dimensions

Bolt Size	1/2 in
Dimension - Height inch	3.44 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6.00 in
Dimension - Width fraction	2-3/4 in
Dimension - Width inch	2.75 in
Dimension - Width mm	70 mm

Conductor Related

Conductor - Copper Str Size Range	2/0 AWG-250 kcmil
Conductor Size	2/0 AWG Str - 250 kcmil
Conductor Type	- CU Tube Std-Size - CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467

Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)