



## GRC34

by Burndy  
Catalog ID: GRC34

Prop 65 Notice

Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 8 AWG (Sol.) - 1/0 AWG (Str.), 3/4" Ground Rod, 3/8" Stud.

Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Slips Over End Of Rod, One-Wrench Installation, UL467 Listed For Direct Burial In Earth And Concrete, Ground Rod Size: 3/4 IN, Stud/bolt Size: 3/8 IN, Width: 19 IN, Length: 0.65 IN, Height: 2.47 IN

## Product Details

### General

Application	For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRC, High Strength
UPC	781810230985
UPC 12 Digit	7818102309855

### Dimensions

Dimension - B Length inch	0.65 in
Dimension - Height inch	2.40 in
Dimension - Length Side B inch	0.65 in
Dimension - Width inch	1.09 in
Dimension - Width mm	28 mm

### Conductor Related

Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Size Range	8 AWG-1/0
Conductor - Rod Size	3/4 in
Conductor Size	#8 AWG Sol - 1/0 AWG Str
Conductor Type	<ul style="list-style-type: none"> <li>Rod-Size</li> <li>CU C Solid-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No

Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

#### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

#### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)