



GX3426

by Burndy
Catalog ID: GX3426

Prop 65 Notice

Cast Cu Alloy Ground Connector, 300 - 500 Kcmil(A), #4 Sol - 2/0 Str
AWG(AA), 3/4" Rod Dia., Bronze H/W

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	357
UPC	781810260715
UPC 12 Digit	7818102607155

Dimensions

Dimension - Height fraction	2-3/4 in
Dimension - Height inch	2.75 in
Dimension - L Length Overall mm	54 mm
Dimension - Length Overall inch	2.12 in
Dimension - Width fraction	1-7/8 in
Dimension - Width inch	1.88 in
Dimension - Width mm	48 mm

Conductor Related

Conductor - Copper Solid Size B	4;3;2;1;1/0;2/0;3/0
Conductor - Copper Str Size A	300;350;400;450;500
Conductor - Copper Str Size A Range	300-500
Conductor - Copper Str Size B	5;4;3;2;1;1/0;2/0
Conductor - Copper Str Size B Range	5-2/0
Conductor - Copper Tube Std Size	0.75
Conductor Type	• CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	8
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)