



GX4C4C

by Burndy
Catalog ID: GX4C4C

Prop 65 Notice

Cast Cu Alloy Ground Connector, #8 Sol - #4 Str AWG(A), #8 Sol - #4 Str AWG(AA), 3/8" Rod Dia., Bronze H/W

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper Alloy
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
U Bolt Type	327
UPC	781810986295
UPC 12 Digit	7818109862955

Dimensions

Dimension - Height fraction	1-7/8 in
Dimension - Height inch	1.88 in
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.62 in
Dimension - Width fraction	1-5/8 in
Dimension - Width inch	1.63 in
Dimension - Width mm	41 mm

Conductor Related

Conductor - Copper Solid Size A	8;7;6;5;4;3
Conductor - Copper Solid Size A Range	8-3
Conductor - Copper Solid Size B	8;7;6;5;4;3
Conductor - Copper Solid Size B Range	8-3
Conductor - Copper Str Size A	9;8;7;6;5;4
Conductor - Copper Str Size A Range	9-4
Conductor - Copper Str Size B	8;7;6;5;4
Conductor - Copper Str Size B Range	8-4
Conductor - Copper Tube Std Size	0.375
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size A • CU C Solid-Size A • CU C Str-Size B • CU C Solid-Size B

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)