



GZ2638

by Burndy
Catalog ID: GZ2638

Prop 65 Notice

Mechanical Grounding Connector, For Copper Cable to Bar, 3 AWG (Str) - 2/0 (Str), 3/8" Stud

Product Details

General

Installation Torque Recommended in-lb	240 LBS/in
Material	Copper
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
UPC	781810232101
UPC 12 Digit	7818102321011

Dimensions

Dimension - Height fraction	2
Dimension - Height inch	2.00 in
Dimension - L Length Overall mm	48 mm
Dimension - Length Overall inch	1.88 in
Dimension - Width fraction	1-5/8 in
Dimension - Width inch	1.59 in
Dimension - Width mm	40 mm

Conductor Related

Conductor - Copper Str Size	3;2;1;1/0;2/0
Conductor - Copper Str Size Range	3-2/0

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	12
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)