



GZ2938

by Burndy
Catalog ID: GZ2938

Prop 65 Notice

Mechanical Grounding Connector, 3/0 AWG (Str) - 250 kcmil, 3/8" Stud

Product Details

General

Installation Torque Recommended in-lb	240 in-lb
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
UPC	781810260777
UPC 12 Digit	7818102607777

Dimensions

Bolt Size	3/8 in
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Height fraction	2-1/4
Dimension - Height inch	2.25 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.34 in
Dimension - Width fraction	2-1/4 in
Dimension - Width inch	2.18 in
Dimension - Width mm	55 mm

Conductor Related

Conductor - Copper Str Size	3/0;4/0;250
Conductor - Copper Str Size Range	3/0-250
Conductor Range	#3/0 AWG (Str) - 250 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)