



GZ4C12

by Burndy
Catalog ID: GZ4C12

Mechanical Grounding Connector, 8 AWG (Str) - 4 AWG (Str), 1/2" Stud

Product Details

General

Installation Torque Recommended in-lb	480 in-lb
Material	Copper Alloy, Cast
Material Type - Screw	DURIUM™ Silicon Bronze
Plated	N
Plating Type	Unplated
UPC	781810990155
UPC 12 Digit	7818109901555

Dimensions

Bolt Size	1/2 in
Dimension - Bar Thickness inch	0.25 in
Dimension - Bar Thickness mm	6 mm
Dimension - Height fraction	1-7/8
Dimension - Height inch	1.88 in
Dimension - L Length Overall mm	42 mm
Dimension - Length Overall inch	1.66 in
Dimension - Width fraction	1-3/4 in
Dimension - Width inch	1.50 in
Dimension - Width mm	38 mm

Conductor Related

Conductor - Copper Str Size	8;7;6;5;4
Conductor - Copper Str Size Range	8-4
Conductor Range	#8 AWG (Str) to #4 AWG (Str)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467

Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)