



GZ4C38

by Burndy
Catalog ID: GZ4C38

Prop 65 Notice

Mechanical Grounding Connector, For Copper Cable to Bar, 8 AWG (Str) - 4 (Str), 3/8" Stud.

Features: High Copper Alloy Ground Connector For Joining A Wide Range Of Cable To 1/4 IN Thick Bar, Cable Is Gripped By Curving It Around The Clamping Bolt In Connector Groove, UL467 Listed, The High Copper Alloy Cast Body And DURIMUM Bolts, Nuts, And Lockwashers Make Them Suitable For Direct Burial In Concrete Or Ground, Installation Torque: 240 IN-LB, Width: 1-1/8 IN, Height: 1-1/2 IN, Bar Thickness: 1/4 IN

Product Details

General

| | |
|---------------------------------------|--|
| Application | For Joining A Wide Range Of Copper Cable To Bar, Direct Burial In Concrete Or Ground |
| Installation Torque Recommended in-lb | 240 in-lb |
| Material | Copper Alloy, Cast |
| Material Type - Screw | DURIUM™ Silicon Bronze |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | MECHANICAL CONNECTOR |
| Type | GZ |
| UPC | 781810260753 |
| UPC 12 Digit | 7818102607533 |

Dimensions

| | |
|---------------------------------|----------|
| Bolt Size | 3/8 in |
| Dimension - Bar Thickness inch | 0.25 in |
| Dimension - Bar Thickness mm | 6 mm |
| Dimension - Height fraction | 1-1/2 |
| Dimension - Height inch | 1.50 in |
| Dimension - L Length Overall mm | 35 mm |
| Dimension - Length Overall inch | 1.38 in |
| Dimension - Width fraction | 1-1/8 in |
| Dimension - Width inch | 1.06 in |
| Dimension - Width mm | 27 mm |

Conductor Related

| | |
|-----------------------------------|------------------------------|
| Conductor - Copper Str Size | 8;7;6;5;4 |
| Conductor - Copper Str Size Range | 8-4 |
| Conductor Range | #8 AWG (Str) to #4 AWG (Str) |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | Yes |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 40 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)