



HSC38FR250

by Burndy
Catalog ID: HSC38FR250

Clear heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - #6, PVC, Fire retardant, Thin Wall, Shrink ratio-2:1, 50 Ft Reel.

Allows inspection of die index embossment and shiner after installation is complete. Should any corrosion occur it will be visible during inspection

Product Details

General

Application	Excellent flame retardant properties and a 2:1 shrink ratio. Tubing enables inspectors to read die index embossments on installed connectors easily
Color	Clear
Construction Material - Main	Polyvinyl Chloride
Material	PVC (polyvinyl chloride)
Sub Brand	VISI-SHRINK
Trade Name	VISI-SHRINK™
Type	HSC-FR
UPC	781810266311

Conductor Related

Conductor Range	#8 AWG to #6 AWG
-----------------	------------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)