



## HSY38T48PF

by Burndy  
Catalog ID: HSY38T48PF

Heat Shrink Tubing, 0.38" ID Min.(Exp.), 0.19" ID Max.(Rec.), #8 - 6, Polyolefin, Shrink ratio-2:1, Thin Wall, Yellow, 4 Ft Reel.

- Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

## Product Details

### General

Color	Yellow
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Material	Polyolefin Aluminum
Material - Body	Aluminum
Number of Pad Holes	1
Plating	No
Style	Impact Extruded
UPC	781810212639

### Dimensions

Diameter - Pad Bolt	0.5 in
---------------------	--------

### Conductor Related

Conductor Diameter (VersaCrimp) - Maximum	0.162 in
Conductor Diameter (VersaCrimp) - Minimum	0.146 in
Conductor Range	#8 AWG to #6 AWG

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)