



K14P6C5P1/OCAG1

by Burndy
Catalog ID: K14P6C5P1/OCAG1

Prop 65 Notice

Dual rated Aluminum Neutral bar for copper and aluminum conductors,
19 Circuits, 14-1/0 AWG , 14-6AWG wire range

Product Details

General

Material	Aluminum
Plated	N
Plating Type	Unplated
UPC	781810665589
UPC 12 Digit	7818106655899

Dimensions

Dimension - Height inch	0.62 in
Dimension - L Length Overall mm	147 mm
Dimension - Length Overall inch	5.77 in
Dimension - Width inch	0.38 in

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - AL Str Size Range	(5) 14-1/0 AWG , (14) 14-6 AWG
Conductor - Copper Str Size Range	(5) 14-1/0 AWG , (14) 14-6 AWG
Number Of Conductors	19

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	Yes
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Carton Quantity	150 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)