



K33B344N

by Burndy
Catalog ID: K33B344N

Prop 65 Notice

Cast Cu Alloy URD Multiple Transformer Terminal, 4 NEMA Holes, 4/0 Str
- 500 kcmil Cu Cable, 9/16" Hole Dia.

Product Details

General

Connector Type	Terminal
Material	Copper Alloy
Physical Attribute - Number of Holes	4
Plated	Y
Plating Type	Tin
Trade Name	KA-LUG™
UPC	781810189207
UPC 12 Digit	7818101892077

Dimensions

Dimension - D inch	3 in
Dimension - F Width Center to Center inch	1.75 in
Dimension - Hole Size fraction	14/25
Dimension - Hole Size inch	0.56 in
Dimension - Length Overall inch	7.09 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - Copper Str Size	4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	4/0 AWG-500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)