



KA2UG7

by Burndy
Catalog ID: KA2UG7

Prop 65 Notice

Universal Terminal, #14 - 2 Stranded Aluminum/Copper; AL9CU; hex head screw 1/4"; Recommended torque 50 lb-in

Product Details

General

Material	Aluminum
Physical Attribute - Number of Holes	1
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin Plated
Type	Bolted Lugs & Terminals
UPC	781810541098

Dimensions

Dimension - Height inch	0.55 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	29 mm
Dimension - Length Overall inch	1.16 in

Conductor Related

Conductor - AL Str Size Range	2 Str. - 14 Str.
Conductor - Copper Str Size	2 Str. - 14 Str.
Conductor Type	CU C Str-Size
Number Of Wires	1

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1800 EA
Minimum Pack Quantity	10000

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)