



KA30226U

by Burndy
Catalog ID: KA30226U

Prop 65 Notice

Universal Terminal, #2 Stranded - 300 kcmil if ONE conductor; #4 Stranded - 1/0 Stranded if TWO conductor; CSA Certified, UL Listed

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	275 LBS/in
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810654507

Dimensions

Dimension - D inch	1.31 in
Dimension - Height inch	1.50 in
Dimension - L Length Overall mm	59 mm
Dimension - Length Overall inch	2.31 in
Dimension - N inch	0.25 in
Dimension - Stud Size inch	5/16
Dimension - Width inch	0.85 in
Dimension - Width mm	22 mm

Conductor Related

Conductor - Copper Str Size Range	2 Str. - 300 Kcmil or (2) 4 Str. - 1/0 Str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	150 EA
-----------------	--------

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)