



KA36229U

by Burndy
Catalog ID: KA36229U

Prop 65 Notice

#4 Stranded - 600 kcmil conductor for ONE conductor; 1/0 - 250 kcmil range for TWO conductor; dual rated AL9CU, CSA Certified; UL Listed

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	550 LBS/in
Material	Aluminum
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810654514

Dimensions

Dimension - D inch	1.50 in
Dimension - Height inch	1.81 in
Dimension - L Length Overall mm	71 mm
Dimension - Length Overall inch	2.81 in
Dimension - N inch	0.63 in
Dimension - Stud Size inch	3/8
Dimension - Width inch	1.38 in
Dimension - Width mm	35 mm

Conductor Related

Conductor - Copper Str Size	4 Str. - 600 kcmil or (2) 250 kcmil - 1/0 Str.
Conductor - Copper Str Size Range	4 Str. - 600 kcmil or (2) 250 kcmil - 1/0 Str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	60 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)