



KA36UAR

by Burndy
Catalog ID: KA36UAR

Prop 65 Notice

Dual Rated for copper and aluminum; aluminum alloy; tin plated; bottom anti-rotational tab; CSA Certified, UL Listed; #4 Stranded - 600 kcmil Copper/Aluminum

Product Details

General

Installation Torque Recommended in-lb	375 LBS/in
Plated	Y
Plating Type	Aluminum Tin Plated
Temperature Rating	194
Type	Bolted Lugs & Terminals
UPC	781810654491

Dimensions

Dimension - D inch	1.37 in
Dimension - Height inch	1.57 in
Dimension - Hole Size inch	0.41 in
Dimension - Hole Size mm	11 mm
Dimension - L Length Overall mm	75 mm
Dimension - Length Overall inch	2.75 in
Dimension - Width inch	1.38 in
Dimension - Width mm	35 mm

Conductor Related

Conductor - Copper Str Size	4 ;600
Conductor - Copper Str Size Range	4 Str. - 600 Kcmil
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Carton Quantity	60 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)