



KAPO750

by Burndy
Catalog ID: KAPO750

Prop 65 Notice

750 kcmil pin adaptor, Torque: 500 N lb, Voltage: 600 V.

- AL9CU Dual Rated for both copper and aluminum conductor
- Listed to UL Wire Connector Standard UL486A-486B
- Rated for use with Fine Strand Conductor
- 600 Volt Rated
- Range Taking conductor port
- Plastisol insulated covers provided with each connector

AL9CU- UL Listed for use with fine strand conductor

Product Details

General

Application	Terminate "upsized" conductor and/or fine strand conductor into mechanical connectors found in molded case circuit breakers, panel board equipment, and other switchgear.
Hex Key	1/2 in
Installation Torque Recommended in-lb	500
Sub Brand	Pin Adaptor
Type	350 - 750 Mechanical Pin Adaptor; Off-Centered Pin
UPC	621945493377

Dimensions

Dimension - Strip Length inch	2.30 in
Height	2.37 in
Length	4.46 in
Outside Diameter	1.75 in
Width	1.87 in

Electrical Ratings

Amperage Rating	535 A
-----------------	-------

Conductor Related

Conductor - AL Str Size Range	#6 - 1/0 AWG
Conductor - Copper DLO Size Range	#6 - 1/0 AWG
Conductor - Copper Flex H Size Range	#6 - 1/0 AWG
Conductor - Copper Flex I Size Range	#6 - 1/0 AWG
Conductor - Copper Flex K Size Range	#6 - 1/0 AWG
Conductor - Copper Str Size Range	#6 - 1/0 AWG

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)