



## KAUKIT4

by Burndy  
Catalog ID: KAUKIT4

Prop 65 Notice

Al Transformer Lug Kit, 500 kVA.

**Features:** These Dual-Rated Lugs Are Constructed From High Strength Aluminum Alloy And Electro Tinned To Provide Low Contact Resistance, Lugs And Mounting Hardware Packaged Together In These Kits, UL Listed AL9CU Dual Rated Set Screw Terminals And CSA Certified, Ensure The Transformer Feeders And Taps Are Terminated Properly, Plated Steel Cap Screws And Hex Nuts With Captive Conical Washers Or Individual Belleville Washers, Terminal To Bus Connections Are Made Using Proper Hardware Resulting In True Torque To Pressure Performance, Compensates For Dissimilar Metal Expansion And Contraction, Hardware Packed In Plastic Bag, No Lost Hardware Prior To Installation, Conductor Type: Run: Stranded Aluminum Or Copper, Includes: (7) 1/2-13 X 2 IN, (4) 1/2-13 X 2-1/2 IN, (11) 1/2-13 Hex Head, (15) K2A40U Terminal, (11) 1/2 IN Belleville Washer, (22) 1/2 IN Flatwasher, Transformer Kva Rating Range: 400 - 500 KVA For Single Phase

## Product Details

### General

|             |                                        |
|-------------|----------------------------------------|
| Application | used to provide low contact resistance |
| Material    | Aluminum                               |
| Sub Brand   | UNIVERSAL TERM                         |
| Type        | Bolted Lugs & Terminals                |
| UPC         | 781810600146                           |

### Conductor Related

|                         |                                                                                                                                                                                     |
|-------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - AL Str Size | 300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil;795 kcmil;800 kcmil |
|-------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

### Certifications and Compliance

|                                         |    |
|-----------------------------------------|----|
| Certification - CSA Approved            | No |
| Certification - ETL                     | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized           | No |
| Certification - cULus                   | No |
| Standards - RoHS Compliance Status      | EX |
| UL Listed                               | No |

### Logistics

|                       |                                                                                                                                                       |
|-----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------|
| Minimum Pack Quantity | 1                                                                                                                                                     |
| Package Contents      | (15) K2A40U;(7) 1/2-13 x 2 in, (4) 1/2-13 x 2-1/2 in Hex Head Bolts;(11) 1/2-13 Hex Head Nuts;(22) 1/2 in Flat Washers;(11) 1/2 in Belleville Washers |

For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)