



KC15

by Burndy
Catalog ID: KC15

Prop 65 Notice

Mechanical Grounding Connector, Cable to Flat, 12 - 9 AWG (Str) / 12 - 8 AWG (Sol).

Features: SERVIT POST Used To Ground One Or Two Cables To Steel Structures, Fence Posts, Transformers, Also Used To Tap One Or Two Cables From Bus Bar, One-Wrench Installation, Conductor Type: Run: Commercial Stranded Copper, Commercial Solid Copper, Cross Flats: 1/2, 3/8 IN, Height: 1-1/8 IN, Stud Size: 1/4-20, Dimension B: 3/8 IN

Product Details

General

Application	For Used To Ground One Or Two Copper Cables To Steel Structures, Fence Posts, Transformers, Tap One Or Two Cables From Bus Bar And Direct Burial
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Leaded Bronze Alloy
Stud Installation Torque inch pounds	80 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810254004
UPC 12 Digit	7818102540044

Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.37 in
Dimension - Body Width inch	0.38 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	0.50 in
Dimension - Height fraction	5/8
Dimension - Height inch	0.69 in
Dimension - L Length Overall mm	30.2 mm
Dimension - Length Overall inch	1.19 in
Dimension - Nut Width inch	0.50 in
Dimension - P inch	0.14 in
Dimension - Threads per inch	20
Dimension - Width inch	18 mm

Conductor Related

Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG;9 AWG;8 AWG
Conductor - Copper Solid Size Range	12 AWG-8 AWG

Conductor - Copper Str Size	12 AWG;10 AWG;9 AWG
Conductor - Copper Str Size Range	12 AWG-9 AWG
Physical Attribute - Number of Conductors Accommodated Total	1

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)