



KC22J12T13

by Burndy
Catalog ID: KC22J12T13

Prop 65 Notice

Copper transformer ground connector. Fits all standard EEI-NEMA distribution transformers as tank grounding terminal, Cable Range: 8 Sol. - 2 Sol.

Features: Fits All Standard EEI-NEMA Distribution Transformers As A Tank Grounding Terminal, One-Wrench Installation, Stud Size: 0.6 IN

Product Details

General

Application	For Used To Fit All Standard EEI-NEMA Distribution Transformers As A Tank Grounding Terminal
Installation Torque Recommended in-lb	80 LBS/in
Material	Bronze, Leaded, Commercial
Plated	N
Plating Type	Unplated
Stud Installation Torque inch pounds	80 LBS/in
Sub Brand	SERVIT POST
Trade Name	SERVIT POST™
Type	KC and K2C Series
UPC	781810127872
UPC 12 Digit	7818101278722

Dimensions

Dimension - B Length inch	0.41 in
Dimension - Bolt Size fraction	1/2
Dimension - Cross Flats inch	0.62 in
Dimension - D inch	0.50 in
Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in
Dimension - P inch	0.27 in
Dimension - Threads per inch	13
Dimension - Width inch	25 mm
Dimension - Width mm	22 mm

Conductor Related

Conductor - Copper Solid Size	8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Size Range	2 AWG-10 AWG
Conductor - Copper Str Size Range	3 AWG-10 AWG
Physical Attribute - Number of Conductors Accommodated Total	2

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)