



KK6A31U8

by Burndy
Catalog ID: KK6A31U8

Prop 65 Notice

6 Conductors #6 AWG - 350 kcmil; Dual Rated

Product Details

General

Connector Type	Terminal
Finish Type	Clear Plate
Material	Aluminum
Physical Attribute - Number of Holes	8
Plated	Y
Plating Type	Clear plated
Type	Bolted Lugs & Terminals
UPC	781810666630

Dimensions

Dimension - Height inch	1.5 in
Dimension - L Length Overall mm	171 mm
Dimension - Length Overall inch	6.75 in
Dimension - Stud Size fraction	9/16

Conductor Related

Conductor - AL Str Size Range	12 Str. - 350 Kcmil
Conductor - Copper Str Size Range	12 Str. - 350 Kcmil
Conductor Type	- CU C Str-Size - AL C Str-Size
Number Of Conductors	6
Number Of Wires	6

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12 EA
-----------------	-------

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)