



KK6A44U12

by Burndy
Catalog ID: KK6A44U12

Prop 65 Notice

6 Conductors 350 - 1000 kcmil; Dual Rated

Product Details

General

Connector Type	Terminal
Finish Type	Clear Plate Cms-14
Material	Aluminum
Physical Attribute - Number of Holes	12
Plated	Y
Plating Type	Clear plated
Type	Bolted Lugs & Terminals
UPC	781810666692

Dimensions

Dimension - Height inch	1.88 in
Dimension - L Length Overall mm	267 mm
Dimension - Length Overall inch	10.50 in
Dimension - Pad Width inch	3.44 in
Dimension - Stud Size fraction	9/16

Conductor Related

Conductor - AL Str Size Range	350 Kcmil - 1000 Kcmil
Conductor - Copper Str Size Range	350 Kcmil - 1000 Kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size
Number Of Conductors	6
Number Of Wires	6

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	6 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)