



KK8A31U10

by Burndy
Catalog ID: KK8A31U10

Prop 65 Notice

8 Conductors; #6 AWG - 350 kcmil; Dual Rated

Product Details

General

Connector Type	Terminal
Finish Type	Clear Plate
Material	Aluminum
Physical Attribute - Number of Holes	10
Plated	Y
Plating Type	Clear plated
Type	Bolted Lugs & Terminals
UPC	781810666647

Dimensions

Dimension - Height inch	1.5 in
Dimension - L Length Overall mm	222 mm
Dimension - Length Overall inch	8.75 in
Dimension - Pad Width inch	3.43 in
Dimension - Stud Size fraction	9/16

Conductor Related

Conductor - AL Str Size Range	12 Str. - 350 Kcmil
Conductor - Copper Str Size Range	12 Str. - 350 Kcmil
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • AL C Str-Size
Number Of Conductors	8
Number Of Wires	8

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	12 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)