



## KK8A44U14

by Burndy  
Catalog ID: KK8A44U14

Prop 65 Notice

8 Conductors 350 - 1000 kcmil; Dual Rated

## Product Details

### General

Connector Type	Terminal
Finish Type	Clear Plate Cms-14
Installation Torque Recommended in-lb	550
Material	Aluminum
Plated	Y
Plating Type	Clear plated
Type	Bolted Lugs & Terminals
UPC	781810666708

### Dimensions

Dimension - D inch	6.19 in
Dimension - Height inch	1.88 in
Dimension - Pad Width inch	12.12 in
Dimension - Stud Size fraction	9/16

### Conductor Related

Number Of Conductors	8
----------------------	---

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	6 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)