



KKA36U2N

by Burndy
Catalog ID: KKA36U2N

Prop 65 Notice

Al Universal Terminal, 2 Holes, #2 AWG (STR)-600 KCML, 1/2 IN Stud, 1.75 IN Spacing, 5.50 IN L, Tin Plated

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	550
Material	Aluminum
Material - Hardware	Aluminum
Physical Attribute - Number of Holes	2
Physical Attribute - Number of Screws	2
Physical Attribute - Screw Type	Allen
Plated	Y
Plating Type	Tin
Type	Bolted Lugs & Terminals
UPC	781810124437

Dimensions

Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.25 in
Dimension - Height fraction	1-17/32 in
Dimension - Height inch	1.52 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	140 mm
Dimension - Length Overall inch	5.50 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	1.39 in
Dimension - Stud Size inch	1/2

Conductor Related

Conductor - AL Str Size	2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil
Conductor - AL Str Size Range	2 AWG-600 kcmil
Conductor - Copper Str Size	2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil
Conductor - Copper Str Size Range	2 AWG-600 kcmil

Conductor Type	• AL C Str-Size • CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
Pallet Quantity	36 EA

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)