



KPA4CHEXGR

by Burndy
Catalog ID: KPA4CHEXGR

Prop 65 Notice

Cu Alloy SCRULUG Terminal, W/Grounding Hexagonal Screw, 1 Hole, #4 Str. - #14 Sol., 1/4" Stud

Product Details

General

Connector Type	Terminal
Installation Torque Recommended in-lb	35
Material	Copper Alloy
Number Of Ports	1
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Plated	Y
Plating Type	Tin Plated
Temperature Rating	194
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810172445
UPC 12 Digit	7818101724455

Dimensions

Dimension - Height inch	0.94
Dimension - Hole Size inch	0.27
Dimension - Length Overall inch	1.2
Dimension - N inch	0.3
Dimension - Pad Width inch	0.5
Weight	0.03 lb

Electrical Ratings

Rating - Minimum Voltage	600
--------------------------	-----

Conductor Related

Conductor - Copper Str Navy Size	#23 AWG;#30 AWG;#40 AWG
Conductor - Copper Str Size Range	#4 AWG to #14 AWG;16 mm ² to 2.5 mm ²

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)