



KVS40A

by Burndy Catalog ID: KVS40A

Prop 65 Notice

High-conductivity, non-copper bearing aluminum alloy connector. Spacer bar separates dissimilar conductors. Intended for heavy duty applications, conductor range, Run Cu and Al :400-800.

Features: Three-Piece, High-Conductivity, Non-Copper Bearing Aluminum Alloy Connector With Thick Spacer And Aluminum Hardware, Recommended For Heavy Duty Dissimilar Metal Applications, Spacer Separates Conductors And Provides Long Contact Length, Belled Entrances Prevent Chafing, Permit Easier Assembly Of Conductors, Longer Peened Bolt Permits Swivel Action For Easier Installation, Neoprene Ring Prevents Loss Of Shorter Bolt, PENETROX Joint Compound Recommended With Aluminum And ACSR, Conductor Type: Run And Tap: Commercial Stranded Copper, Commercial Stranded Aluminum, ACSR, 5005, AAAC, Stud/bolt Size: 1/2 IN, Length: 2-7/16 IN, Installation Torque: 300 IN-LB, Width: 2-7/8 IN, Height: 4-1/16 IN, Conductor Spacer: Yes

Product Details

General

Application	For All Combinations Of Copper, Aluminum, ACSR, AAAC And 5005
Sub Brand	OKLIP
Туре	KVS
UPC	781810073506

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)