



KVSW26

by Burndy
Catalog ID: KVSW26

Prop 65 Notice

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 2 str. - 2/0 str., Tap: 6 sol. - 2/0 str.

Product Details

General

Installation Torque Recommended in-lb	180 LBS/in
Material	Copper
Plated	N
Plating Type	Unplated
Trade Name	OKLIP™
UPC	781810065457
UPC 12 Digit	7818100654577

Dimensions

Dimension - Height inch	1.76 in
Dimension - Length Overall inch	1.04 in
Dimension - Stud Size inch	5/16 in
Dimension - Width inch	1.56 in

Conductor Related

Conductor - Copper Solid Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Tap Range	6 AWG-2/0 AWG
Conductor - Copper Str Run	2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Run Range	2 str. - 2/0 str.
Conductor - Copper Str Tap	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG
Conductor - Copper Str Tap Range	6 sol. - 2/0 str.
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)