



KVSW44

by Burndy
Catalog ID: KVSW44

Prop 65 Notice

Mechanical Connector For CUWeld and Copper Supplied with a CU alloy Spacer that separates run and tap conductors, Run: 500-1000 Kcmil, Tap: 250-1000 Kcmil.

Features: Type KVS Except For A High Copper Alloy Spacer That Separates Run And Tap Conductors, Provides High Contact Pressure, Confines Conductor Strands, And Assures Vibration-Proof Connection, Longer Peened Bolt, Permits Swivel Action For Easier Installation, Silicon Bronze DURUM Hardware, Installation Torque: 500 IN-LB, Conductor Type: Run: Copperweld, Commercial Stranded Copper, Conductor Spacer: Yes

Product Details

General

| | |
|---------------------------------------|--------------------------------------|
| Application | For Copper And Copperweld Conductors |
| Installation Torque Recommended in-lb | 660 LBS/in |
| Material | Copper |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | OKLIP |
| Trade Name | OKLIP™ |
| Type | KVSW |
| UPC | 781810068052 |
| UPC 12 Digit | 7818100680522 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Height inch | 4.14 in |
| Dimension - Length Overall inch | 1.04 in |
| Dimension - Stud Size inch | 5/8 in |
| Dimension - Width inch | 1.56 in |

Conductor Related

| | |
|----------------------------------|--|
| Conductor - Copper Str Run | 500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil |
| Conductor - Copper Str Run Range | 500 kcmil- 1000 kcmil |
| Conductor - Copper Str Tap | 250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;550 kcmil;600 kcmil;700 kcmil;750 kcmil;800 kcmil;850 kcmil;900 kcmil;1000 kcmil |
| Conductor - Copper Str Tap Range | 250 kcmil - 1000 kcmil |
| Conductor Type | CU C Str-Size |

Certifications and Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |

| | |
|------------------------------------|----|
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)