



MCC1000

by Burndy
Catalog ID: MCC1000

Prop 65 Notice

Manual Cable Cutting Tool, 1000 kcmil Copper(Max), 1000 kcmil Aluminium(Max).

- High quality design and construction
- Rugged high quality steel blades
- Fiberglass handles with soft grips

Features: The MCC Series Cable Cutters Are Precision Cable Cutters Incorporating High Leverage Shear-Type Design Capable Of Cutting Up To 1000 KCMIL Copper And Aluminum Cables, Rugged Steel Blades And Fiberglass Construction Provide Cutting Ease, Long Life And Minimum Cable Distortion, MCC20 Has Nonslip Grip Covered Forged Steel Handles, High Quality Design And Construction, Rugged High Quality Steel Blades, Fiberglass Handles With Soft Grips, MCC20 Has Forged Steel Handles With Non-Slip Grips, Easy Cutting With Minimal Cable Distortion, Excellent Cutting Edge Performance, Provides Comfortable Tool Operation And Long Life, Width: 6 IN, Weight: 9 LB1 year limited warranty (excluding blades)

Product Details

General

Application	Cutting
Sub Brand	HYTOOL
Tool Type	Manual Cable Cutters
Type	Cutters
UPC	781810174869
UPC 12 Digit	7818101748699

Dimensions

Cable Insulation Diameter Maximum	1.900 in
Length	32 in
Weight	9 lb
Width	6 in

Conductor Related

Crimping Ranges	Cutting Capacity : Copper upto 1000 kcmil; Aluminum: upto 1000 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)