



MD734R

by Burndy
Catalog ID: MD734R

Prop 65 Notice

Hand operated full cycle ratchet tool, Hytool, Handle material: Reinforced composite Polymer, Crimp Force: 9000 lbs.

- Full stroke ratchet mechanism
- Ergonomically designed one-piece composite polymer handles
- Comfort grip handles
- Time-proven forged steel jaw design
- No tool adjustment required
- Positive lock spring-loaded die retainer buttons
- PTFE impregnated steel/bronze bushings and stainless steel pins
- Color coded dies
- Die index embossed on finished connection for inspectability

Features: Full Stroke Ratchet Mechanism, Ergonomically Designed, One Piece, Composite Polymer Handles, Comfort Grip Handles, Time-Proven Forged Steel Jaw Designs, No Tool Adjustment Required, Positive Lock, Spring Loaded Die Retainer Buttons, PTFE Impregnated Steel/Bronze Bushings And Stainless Steel Pins, Color Coded Dies, DIE Index Embossed On Finished Connection, Easier Tool Operation Due To Unique Handle Design, And Anti-Slip Grips, Grips And Handle Knobs Improve Operation By Preventing Slipping, Butting Jaws Assure Proper Crimps, Wear Indicator Allows Instant Inspection Of Calibration, Full Cycle Ratchet Assures Complete Consistent Crimp, High Grade Hardware Increases Tool Life And Durability, Allows Use Of Complete Line Of BURNDY W-VT, W-RT And X-RT Series Dies, Color Coded Dies Simplify Selection Of Correct Connector And Die Combinations, Die Index Embossment On Crimp Provides Easy Inspection And Quality Assurance, 99,000 Crimps Without Needing Adjustment, 5-Year Limited Warranty, Width: 8 IN At Handles, 4-1/2 IN At Jaws, Jaw Covering: EPDM Rubber (MD7-34RC), Covered Handles: No, Permanent Dies: Yes, Handle Length: 26 IN, Dies Used: W VT, V RT And X RT, Weight: 8 LB, Accepts Dies: Yes, Fully Covered: No, Cutting Dies Available: Yes 5 year limited warranty

Product Details

General

Application	Copper Lugs and Splices #8-500 kcmil Types YA, YA-L, YA-L-TC, YA-L-NT,YS-L, YS, YST, YA-TC
Crimp Force Capacity	4.5 ton
Die Type	W-VT, W-RT, and X-RT Styles
Sub Brand	HYTOOL
Tool Type	Hand Operated Crimper
Trade Name	POSI-PRESS™ HYTOOL™
Type	Crimpers
UPC	781810040430
UPC 12 Digit	7818100404300

Dimensions

Length	25 in
Weight	7 lb
Width	8 in

Conductor Related

Crimping Ranges

Copper Lugs/Splices #8 - 500 kcmil, Copper Lugs/Splices #8 - 350 kcmil Flex, Copper Battery Lugs #8 - 350 kcmil Flex, Thin Wall C-Taps #12 - 3/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)