



MR15

by Burndy
Catalog ID: MR15

Full Cycle Ratchet Crimping Hand Tool, 22-10 AWG.

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

Features: The Types MR15 Series HYTOOL Incorporate A Full Cycle Ratchet Mechanism That Provides A Complete, Positive Crimp Each Time, Once Started The Ratchet Mechanism Does Not Allow The Handles To Be Opened Until After The Full Ratcheting Cycle Is Completed, Unless The User Actuates The Emergency Release Lever, This Provides For A Completed Crimp Before A Connector Can Be Removed From The Tool, UL Listed For Use With BURNDY Connectors, Fully Ratcheted Tool To Assure Properly Crimped Connections, Easy Groove Identification With Color Coded Dies, Maximum Crimping Comfort Grips, Compact, Narrow Nose To Work In Confined Areas, 5-Year Limited Warranty, Wire Cutter: No, Dieless: Yes, Weight: 1.10 LB, Type Of Terminals/splices Used On: Vinyl Insulated, Wire Stripper: No, Closed Size: 2.5 IN, Crimps Coaxial Connectors: No5 year limited warranty

Product Details

General

| | |
|--------------|--|
| Application | Used for Nylon insulated terminals(TP, TP-F, TP-Z, TP-LF etc.) and Splices(SP, BS) |
| Sub Brand | HYTOOL |
| Tool Type | Full Cycle Ratchet Crimper |
| Trade Name | HYTOOL™ |
| Type | Crimpers |
| UPC | 781810011888 |
| UPC 12 Digit | 781810011888 |

Dimensions

| | |
|--------|---------|
| Height | 2.50 in |
| Length | 8.88 in |
| Weight | 1.1 lb |
| Width | 6.00 in |

Conductor Related

| | |
|-----------------|---------------|
| Crimping Ranges | #22 - #10 AWG |
|-----------------|---------------|

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | EX |
| UL Listed | No |

Logistics

| | |
|-----------------------|-------|
| Carton Quantity | 20 EA |
| Minimum Pack Quantity | 1 |

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)