



MR18

by Burndy
Catalog ID: MR18

Hand Held Full Cycle Ratchet Crimping Tool, 22 AWG-10 AWG Bare and Insulated Terminals and Splices.

- Permanent die sets
- Heavy duty forged steel frame
- Full cycle ratchet mechanism
- Emergency release
- Comfort grip handles

Features: The Types MR18 Series HYTOOL Incorporate A Full Cycle Ratchet Mechanism That Provides A Complete, Positive Crimp Each Time, Once Started The Ratchet Mechanism Does Not Allow The Handles To Be Opened Until After The Full Ratcheting Cycle Is Completed, Unless The User Actuates The Emergency Release Lever, This Provides For A Completed Crimp Before A Connector Can Be Removed From The Tool, UL Listed For Use With BURNDY Connectors, Fully Ratcheted Tool To Assure Properly Crimped Connections, Easy Groove Identification With Color Coded Dies, Maximum Crimping Comfort Grips, Compact, Narrow Nose To Work In Confined Areas, 5-Year Limited Warranty, Wire Cutter: No, Dieless: Yes, Weight: 1.10 LB, Type Of Terminals/splices Used On: Nylon Insulated, Closed Size: 2.5 IN, Crimps Coaxial Connectors: No, Wire Stripper: No5 year limited warranty

Product Details

General

Application	Used for Nylon insulated terminals(TN,TN-F,YAES, YAES-F) and splices(SN, SNM, YSE-HN, YSES)
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimper
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810011201
UPC 12 Digit	7818100112011

Dimensions

Height	2.50 in
Length	8.88 in
Weight	1.1 lb
Width	6.00 in

Conductor Related

Crimping Ranges	#22 - #10 AWG
-----------------	---------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX

UL Listed	No
-----------	----

Logistics

Carton Quantity	20 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)