

MRE1022B

by Burndy
Catalog ID: MRE1022B

Prop 65 Notice

Ergonomic Ratchet Hand Tool, #22-#10.

- Ratchet mechanism does not allow handles to open until full cycle is complete
- Stop plate ensures proper location for consistent reliable connection
- Die Inspection Gauges available (sold separately)
- Easy groove identification with color coded dies
- Ratchet release lever in case of misalignment

Uninsulated Terminals and Splices, provide a complete positive crimp each time5 year limited warranty



Product Details

General

Application	Crimping
Die Type	Permanent Dies
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimp Tool
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810512982
UPC 12 Digit	7818105129822

Dimensions

Height	1.00 in
Length	10.38 in
Weight	1.3 lb
Width	3.00 in

Conductor Related

Crimping Ranges	Copper: #22 AWG - #10 AWG
-----------------	---------------------------

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	EX

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)