



MY293C

by Burndy
Catalog ID: MY293C

Prop 65 Notice

Dieless Hytool, #8 Str. through 250 kcmil Copper, #8 Str. through 4/0 Str. Aluminium Conductors, 22.65 in L, Wire lug crimping tool.

- Two-ply covered handles on MY29-3C and MY29-11C designs
- Heavy duty forged steel back, body and handles
- Strong reinforced forged steel back
- .31" dia. hole for bench mounting operations
- Comfort grips
- Extra strong, heavy reinforced handles
- Indentor die
- Knurled steel adjusting knob

Features: Save On Capital Investment With The Type MY HYTOOL That Accommodates A Wide Range Of Connector/Conductor Combinations From 8 AWG Stranded - 250 KCMIL, Save Time, Money, And Lower Installed Cost With The Original Dieless MY Tool Design, No Separate Dies Required To Purchase Or To Lose, Fast And Easy Tool Setting For The Connector/ Conductor Combination Simply By Aligning The White Scribe On The Nest Die With The Wire Size On The Gauge For Proper Crimping Results, Easy To Adjust Nest Die With Knurled Steel Knob And Machine Threads, Quality Tool With Precision Machines Indentor, Component Parts And Tool Body, Fast, Medium And High Volume Crimping Is Easily Accomplished By Bench Mounting The Type MY Tool In The BMY-BCH-MT Bench Mount Adapter, A Single Bolt Holds The MY HYTOOL Securely Using The 0.31 IN Diameter Mounting Hole In The Bench Mount Adapter, High Quality Rugged Tool Design Manufactured From Heavy Duty Forged Steel With Strong Reinforced Back And Handles, Covered Handles Available On The MY29-3C, MY29-11C And MY29-3CF HYTOOL, Comfort Grip Handles For Long Periods Of Usage, Compression Terminals And Splices Are UL Listed And CSA Certified When Installed With Type MY HYTOOL, 5-Year Limited Warranty, Case And Lugs: No, Covered Handles: Yes, Conductor Type: Copper Navy, Weight: 8 LB, Accepts Dies: No, Fully Covered: No, Cutting Dies Available: No, Permanent Dies: Yes5 year limited warranty

Product Details

General

Application	TOOL CONNECTORS MY29-3, MY29-3C Copper-YA, YA-L, YS-L, MY29-3CF Aluminum-YA-A, YS-A, MY29-11 Copper-YA, YA-L, YS, MY29-11C YAV-FX,YS-L, YAV-L, YSV-L, MY28 YAV-L, YSV-L, MY28-4 YAV-A-L, YSV-A-L, YAV-A-R, MY28-6 YAE-L, YAEV-RS, YAEV-H, YAEV-RH
Die Type	Dieless
Finish Type	Black Matte
Sub Brand	HYTOOL
Tool Type	Dieless Mechanical Compression Tools
Trade Name	HYTOOL™
Type	Crimpers
UPC	781810462102
UPC 12 Digit	7818104621022

Dimensions

Height	1.12 in
Length	22.65 in
Weight	8 lb

Width	4.86 in
-------	---------

Conductor Related

Crimping Ranges	#8 Str. - 250 kcmil, 30 Navy - 250 Navy, #8 Str. - 4/0 Str
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)