



OUR840

by Burndy
Catalog ID: OUR840

Prop 65 Notice

Full Cycle Hand Operated Ratchet Tool, 8000 lbs Crimp Force, 8 AWG-250 kcmil Copper, 8 AWG-4/0 AWG Aluminium, W and X Dies.

- Spring loaded positive lock die retainer buttons
- 1/4 hole for snap fastener
- Butting surfaces provide visual check for tool adjustments
- Spring loaded handle
- High strength steel
- Rugged and protected ratchet mechanism
- Heat treated steel construction
- Comfort grip handles

Features: The OUR840 Incorporates A Full Cycle Ratchet And Cam Mechanism Allowing An Easy, One Hand Crimping Action, Designed For Low Maintenance Operation, The Ratchet Mechanism Provides For Properly Completed Crimps Every Time Before The Tool Can Be Removed From The Connection, With Nest And Indentor Dies, It Will Install 5/8 IN INSULINK And LINKIT Service Entrance Connectors With Only One (1) Crimp Per End, With The Use Of Reduced Handle Force X Dies, Additional Splices, Taps, And Terminals Can Be Properly Installed, The Die Inserts Snap Into The Permanent Groove Easily With One Hand And Lock Securely In The Tool With The Spring Loaded Positive Lock Die Retainer Buttons, Tool Operation Is Simple: Slip The Tool Over The Connector, The First Few Strokes Grip The Connector, Stroke Until Automatic Tool Release Signifies A Completed Compression, Allows Proper Crimping Of Sleeves And Terminations In Crimping Underground Applications, Proper Crimps Are Assured With Butting Surface Inspection And Full Cycle Ratchet Mechanism, Uses Reduced Handles Force X Dies, One Tool For Most Service Applications, Improved Service Through Redesign And Improvement Of Many Internal Parts, Easy Visual Field Check For Proper Tool Adjustment With Butting Surfaces, Easier Tool Operation Is Provided With Mini Strokes And Anti-Slip Grips, Nest And Indenter Dies Available, W-28K Cutter Die Permits Use Of OUR840 Tool As A Cable Cutter, Conductor Range: 4 - 4/0 AWG ACSR, Aluminum And Copper, UL Listed Connections When Color Coded X Dies Are Used On BURNDY Connectors, 5-Year Limited Warranty, Handle Input Force: 8 LB, Accessories: PT4583 Leather Holster, OUR840-WC Metal Carrying Case With Die Tray, Weight: 2.14 LB, Wire Stripper: No, Dieless: No, Crimps Coaxial Connectors: No, Wire Cutter: Yes 5 year limited warranty

Product Details

General

Application	Crimping
Die Type	W & X dies
Sub Brand	HYTOOL
Tool Type	Full Cycle Ratchet Crimp Tool
Trade Name	POPPER™ HYTOOL™
Type	Crimpers
UPC	781810408537
UPC 12 Digit	7818104085377

Dimensions

Height	1.30 in
Length	13.00 in
Weight	2.875 lb

Width	3.75 in
-------	---------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 250 kcmil; Aluminum: #8 AWG to 4/0 AWG
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)