



PAT46LWLI

by Burndy Catalog ID: PAT46LWLI

Prop 65 Notice

Hydraulic Self Contained Battery Actuated tool with 120V Charger, 15 Tons, 18 V Li-Ion.

- 2" jaw opening
- Used with P dies
- U dies with PUADP1 adapter (sold separately)
- + Light weight, "latch head" with 355° head rotation
- Ergonomically balanced

Cu:#8 AWG str., 1500 kcmil, grounding: to 500 kcmil, YGA, YGHA, YGFTerminals, uninsul: #8 to1500 kcmil: YA, YA-2N, YA-L,YA-LB, YA-TC, YA-2LN,YAB-4N, YAV-L, ,YAV-RS, YA-TC-FX,Terminals, insul: #8 to 2/0,YAEV,Splices: #8 to 1500 kcmil,YS, YS-T, YS-L, YS-LB, YST,YSP-T, YGS, YGHS Taps:YH, YCHC #14 to 1000 kcmil,YC-C to 4/0 AWG,Taps, grounding: to 500 kcmilYGHC-C, YGHP-C, YGHR-C, AI #8 AWG -1250 kcmil YA-A, AYP, AYPO, Splices:YS-A, YS-AT, YRB, Taps:YFD, YFN, YFO, YFR5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime Warranty on INFINITY DRIVE*

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	15 ton
Die Type	P and U style (with PUADP1)
Recharge Time	0.5 h
Sub Brand	PATRIOT [®] CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Туре	Crimpers
UPC	781810654675
UPC 12 Digit	7818106546755

Dimensions

Height	13.93 in
Jaw Width	2 in
Length	18.59 in
Weight	16.8 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #14 AWG - 1500 kcmil; Aluminum: #8 AWG - 1250 kcmil
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No
Logistics	

LOGISTICS

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)