



PAT4PC834LI

by Burndy Catalog ID: PAT4PC834LI

Prop 65 Notice

4 Point C-Head Dieless Tool, Hydraulic, 6 Ton, 18V Lithium Ion.

- Dieless system
- Range taking capabilities
- 360° head rotation
- Ergonomically balanced

Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics for ultimate reliability in the harshest environments5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	Dieless
Recharge Time	0.5 h
Sub Brand	PATRIOT [®] CRIMPER
Tool Type	Battery Operated Dieless 4 - Point Crimper
Trade Name	PATRIOT®
Туре	Crimpers
UPC	781810505441
UPC 12 Digit	7818105054411

Dimensions

Height	14.1 in
Length	15.6 in
Weight	13.2 lb
Width	3.2 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG - 1000 kcmil; Copper Flex: #8 - 777.7 kcmil; Aluminum: #8
	- 750 kcmil

Certifications and Compliance

Certification - CSA Approved	No	

Certification - ETL	No	
Certification - UL Recognized	No	
Certification - cULus	No	
Standards - RoHS Compliance Status	EX	
UL Listed	No	
Logistics		

1

Minimum Pack Quantity

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)