



PAT600LI

by Burndy
Catalog ID: PAT600LI

Prop 65 Notice

Battery Actuated Crimping Tool, Hydraulic Self Contained, 6 Ton Output Force, 8 AWG-600 kcmil Copper, 8 AWG-350 Aluminium, W, X, W-VT Dies, 18V Lithium Ion.

- Specialized latch head design
- Ergonomic design allows one hand operation for Ram advance and Ram retraction
- 180 degree head rotation
- Permanent D3 crimp groove accepts all W Dies
- Enhanced clearance for tap connections

Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics for ultimate reliability in the harshest environments 5 Year Limited Warranty on Tool, 3 Year on Batteries and Charger, Lifetime warranty on INFINITY DRIVE

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	W, X, W-VT style dies
Recharge Time	0.5 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810505328
UPC 12 Digit	7818105053288

Dimensions

Height	13.7 in
Length	14.5 in
Weight	10.1 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG-600 Kcmil; Copper Flex: #8 AWG-350 Kcmil Flex; Aluminum: #8 AWG-350 Kcmil
-----------------	------------------------------------------------------------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)