



PAT81KFTLI

by Burndy
Catalog ID: PAT81KFTLI

Prop 65 Notice

Dieless Crimper, 6 Ton, 18 V-DC, Recharge Time 45 mins.

- Dieless system
- Range taking capabilities
- 360° head rotation
- Mechanical ram release (no battery consumption)
- Overmolded handle for comfort and improved grip
- Durable high impact formed carrying case

Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics - ultimate reliability in the harshest environments 5 Year Limited Warranty on Tool, 3 year on batteries/ charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	Crimping
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Die Type	Dieless
Recharge Time	0.5 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Operated Dieless 4 - Point Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810505380
UPC 12 Digit	7818105053800

Dimensions

Height	14.1 in
Length	15.6 in
Weight	13.2 lb
Width	3.2 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Copper: #8 AWG -1000 kcmil; Copper Flex: #8 AWG - 777.7 kcmil; Aluminum: #8 AWG- 750 kcmil
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)