



PATCUT129LI

by Burndy
Catalog ID: PATCUT129LI

Prop 65 Notice

Battery powered crimping tool, 14.5 in L, 3.5 in W, 18 V-DC.

- Special Latch head design provides interference free closure for Mid-Span cuts
- 180° head rotation
- Overmolded handle and ergonomic design
- One-handed operation for advance, retract and hold
- Durable high impact carrying case

Length: 14.5 IN, Width: 3.5 IN, Height: 13.5 IN, Operating Voltage: 18 VDC, Recharge Time: 30 MINT, Accessories: PATCHGR-LI 120 VAC Charger, PT208620 Lanyard, BAT18VLI Replacement Battery, Battery Type: Li-Ion, Operating Pressure: 10000 PSI, Covered Head: No, Number Of Conductors Accomodated (max): Ground Rod Up To 5/8 IN, EHS Guy Strand Up To 3/8 IN, Soft Steel Bolts Up To 5/8 IN, Rebar Up To 1/2 IN, Aluminum - 1.29 IN Diameter, Standard Guy Strand Up To 1/2 IN, Copper - 1.29 IN Diameter, Weight: 10.2 LB5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	Cutting
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	7 ton
Recharge Time	0.5 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	781810505212
UPC 12 Digit	7818105052122

Dimensions

Height	13.5 in
Length	14.5 in
Weight	10.2 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum Cable: upto 1.29"; ACSR: upto 1113 Kcmil; Ground rod: upto 5/8"; Rebar: upto 1/2"; Soft steel bolts: upto 5/8"; Standard Guy: upto 1/2"; EHS Guy: upto 3/8"
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (2) 3Ah 18V li-ion batteries, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)