

PATCUT2156L5

by Burndy
Catalog ID: PATCUT2156L5

Prop 65 Notice

PATRIOT 2156 ACSR LATCH-HEAD CUTTER, 5.0 AH LITHIUM-ION BATTERY.

REFINED HYDRAULIC SYSTEM FOR ULTRA PERFORMACE, SPEED AND RELIABILITY; FIELD PROVEN ELECTRONICS FOR ULTIMATE RELIABILITY IN THE HARSHTEST ENVIRONMENTS; 180 degree Head rotation; MECHANICAL RAM RELEASE: PROVIDES CONSISTENT, RELIABLE RAM RETRACTION,(NO BATTERY POWER CONSUMPTION)5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



Product Details

General

Application	Cutting
Battery Type	5.0 Ah Li-Ion
Recharge Time	0.75 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	621945471078

Dimensions

Height	13.66 in
Length	16.46 in
Weight	15.5 lb
Width	3.27 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum Cable: upto 2.0"; ACSR: upto 2156 Kcmil; Ground rod: upto 3/4"; Rebar: upto 5/8"; Soft steel bolts: upto 3/4"; Standard Guy: upto 9/16"; EHS Guy: upto 9/16";
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)