

PATCUT2156LI

by Burndy
Catalog ID: PATCUT2156LI

Prop 65 Notice

Battery Actuated Latch Cutter With 120V Charger, 18 V Li-Ion.

- 180° head rotation
- Durable hardened steel blades
- Specialized latch head for mid-span cuts
- Mechanical ram release with no power consumption

Durable Hardened Steel Blades for Optimum Cutting and Increased Life, Battery Powered Cutting Technology for Easy Tool Operation and Portability, Tool Weight: 15.5 Lbs, Operating Voltage: 18V-DC, Recharge Time: 30 Mins, 180 Deg Head Rotation Provides Versatile Head Positioning Allows User to Get Into Tight Areas Easier 5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Cutting
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	10 ton
Recharge Time	0.5 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	781810636299
UPC 12 Digit	7818106362999

Dimensions

Height	13.46 in
Length	16.47 in
Weight	15.5 lb
Width	3.27 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum Cable: upto 2.0"; ACSR: upto 2156 Kcmil; Ground rod: upto 3/4"; Rebar: upto 5/8"; Soft steel bolts: upto 3/4"; Standard Guy: upto 9/16"; EHS Guy: upto 9/16";
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	UI
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (2) 3Ah 18V li-ion batteries, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)