

# PATCUT245LIDC

by Burndy  
Catalog ID: PATCUT245LIDC

Prop 65 Notice

Latch Head, Cu/Al up to 2.45" O.D. Hydraulic Self Contained Battery Actuated tool, 6 Tons, 18V with 12V DC Charger, 18V 3.0Ah Lithium Ion.

- 180° head rotation
- Cuts up to 2.45" diameter copper/aluminum cable
- Specialized latch style cutting head for interference-free closure for mid-span work
- Ergonomic design, overmolded handle

5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



## Product Details

### General

Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Recharge Time	0.5 h
Tool Type	Battery Actuated Cutting Tool
Type	Cutters
UPC	781810505274
UPC 12 Digit	7818105052744

### Dimensions

Height	13.5 in
Length	14.5 in
Weight	10.2 lb
Width	3.5 in

### Electrical Ratings

Operating Voltage	18V DC
-------------------	--------

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity

1

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)