

PATCUT245LI

by Burndy
Catalog ID: PATCUT245LI

Prop 65 Notice

Battery Cutter Tool, up to 2.45" O.D Cu & Al, 18V Li-ion, 120V AC Charger

- 180° head rotation
- Cuts up to 2.45" diameter copper/aluminum cable
- Specialized latch style cutting head for interference-free closure for mid-span work
- Ergonomic design, overmolded handle

Features: Refined hydraulic system for ultra performance, speed and reliability, Field proven electronics for ultimate reliability in the harshest environments, Overmolded handle for comfort and improved grip, allows for one-handed operation for advance, retract, and hold, Specialized latch head design for interference free closure for mid-span cuts, 18-volt Lithium-Ion batteries provide 2.5 times more charge/discharge cycles than traditional Ni-Cd batteries and provide 430 percentage more lifetime work, 30 minute charger controls current, voltage and temperature to maximize battery life, Forced air cooling fan cools the battery by forcing cool air through the battery's built-in air vents, 180 DEG head rotation allows user to get into tight areas easier, Ergonomically balanced tool design eases operation and lessens fatigue, Durable high impact formed carrying case provides superior protection and stores all accessories, 5-year limited warranty on tool (excluding blades), Lifetime warranty on INFINITY DRIVE, 1-year warranty on batteries and charger 5 year limited warranty, 3 year on batteries and charger, Lifetime warranty on INFINITY DRIVE®



Product Details

General

Application	Cutting
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	6 ton
Recharge Time	0.5 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	781810505243
UPC 12 Digit	7818105052433

Dimensions

Height	13.5 in
Length	14.5 in
Weight	10.2 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Copper/Aluminum Cable: upto 2.45"
-----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
Package Contents	Tool, (2) 3Ah 18V li-ion batteries, charger, lanyard and case

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)