

PATCUT4CUALLI

by Burndy
Catalog ID: PATCUT4CUALLI

Prop 65 Notice

Battery powered crimping tool with 110V charger.

- Extra wide jaw opening
- Scissor action cutting jaws
- 355° head rotation
- Multi-position assist handle
- Durable high impact formed carrying case

Refined hydraulic system for ultra performance, speed and reliability
5 Year Limited Warranty on Tool(excluding blades), 3 year limited warranty on the batteries and charger, Lifetime warranty on INFINITY DRIVE



Product Details

General

Application	Cutting
Battery Type	3.0 Ah Li-Ion
Crimp Force Capacity	11 ton
Recharge Time	0.5 h
Sub Brand	PATRIOT® CUTTER
Tool Type	Battery Actuated Cutter
Trade Name	PATRIOT®
Type	Cutters
UPC	621945437944
UPC 12 Digit	6219454379444

Dimensions

Height	15.33 in
Length	24.31 in
Weight	20.3 lb
Width	3.26 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	Cutting Capacity: Copper & Aluminum : upto 4.0" OD
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Logistics

Minimum Pack Quantity

1

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)